



#### MACHINE DESCRIPTION

The wireless transplanter RW5 with continuous planting using **up to 12 fingers** for transplanting on a max working width to 1000 mm.

First machine on the market with singularly motorized fingers without cables, to ensure less maintenance, and more flexibility with every kind of trays on the market.


TECHNICAL DATA	M.U.	RW5
FINGER PRODUCTION	cycle/hour	800
TRAYS WIDTH (max)	mm	600
WEIGHT	kg	630
INSTALLED POWER	kW	1,8
AIR CONSUMPTION (max)	l/min	80


#### **TECHNICAL SPECIFICATIONS**

- Singulary motorized wireless finger.
- Electric panel, programming and autodiagnostic with 5,7" colour touch-screen.
- Possibility of different multiple destination programs.
- Possibility of side source to avoid the leafage damage.
- Finger easy to remove, with minimum interaxis of 31 mm.
- Single command opening/closing of needles.

DETAILS page 74

ACCESSORIES page 75







# **DETAILS**TRANSPLANTER



**Fingers removable** by hand without using any tool.

#### **INCLUDED ON:**

**ALL TRANSPLANTER** 



**Pot positioning** on the belt with cylinders (diameter pots from 9 to 20 cm).

#### INCLUDED ON:

RW8POTS

WURBINATI



Multicolour function: enables to program the **transplanting of different varieties** in the same tray.

#### INCLUDED ON:

RW64, RW32



The exclusive flat profile of the needles and the closing system allow an excellent grip of the plug even with weak-rooted plants.

#### INCLUDED ON:

ALL TRANSPLANTER

#### **PROGRAMMING**

Examples of programming on the board with a colour touch-screen system and an innovative graphic software for the operator easy to use.




**Main menu** to enter into different functions.



**State of the machine** with selected program number.




**Program function** with option of **plug and destination**.



Plug tray dimension.



Destination tray dimension.



**Number of plugs** each pot with or without the central plug and rotation.

### INCLUDED ON: ALL TRANSPLANTER







**Tray block** from top in plug axis for thermoformed trays.



The fingers with the open star are suggested to transplant the forest varieties.



**Final roller belts** available in different lengths; **tray holders** and limit switch on request.



With the **3 axis transplanting selection**, the machine can be set with two destination areas: **one for trays and the other one for pots**.

AVAILABLE ON:

ALL TRANSPLANTER

**AVAILABLE ON:**ALL TRANSPLANTER

ALL TRANSPLANTER

AVAILABLE ON:

L TO ANICOL ANITED

Plug tray denester with young plants.



AVAILABLE ON:

ALL TRANSPLANTER

## **SUB-IRRIGATION**

The SUB-IRRIGATION machine is mainly recommended when a uniform watering is needed or when the watering from above is not enough.

It can be integrated to a seeding/transplanting line or used as independent machine.

The sub-irrigation guarantees humidity to the plant's clod and the option to water also the leaves (selecting the drilled bars).



AVAILABLE ON:

ALL
TRANSPLANTER